

Disposable reservoirs

Multi-channel reagent reservoirs



Our multi-channel reservoirs are superior in every way with thicker walls, crush-resistant ‘turrets’ at the corners, easy pour-spouts, 25mL graduation marks, and tabs to prevent stacked reservoirs from sticking together.

- Tapered reservoir bottoms create narrow trough to aid full sample recovery
- Sterile versions are individually sealed in sani-tear HDPE packets and gamma-irradiated
- Disposable

Cat No.	Volume	Sterility	Material	L x W x H	Pack qty
11314035	55mL	Non-sterile	Clear PVC	14.5 x 8.5 x 2.5cm	100
11324035	55mL	Non-sterile	White polystyrene	14.5 x 8.5 x 2.5cm	100
11334035	55mL	Sterile	White polystyrene	14.5 x 8.5 x 2.5cm	50 Pk
11344035	100mL	Non-sterile	White polystyrene	14.5 x 8.5 x 2.5cm	100
11354035	100mL	Sterile	White polystyrene	14.5 x 8.5 x 2.5cm	50

© 2017 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at fishersci.com/trademarks.

Austria: +43(0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20
Germany: +49 (0)2304 9325 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478
Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00
Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303
Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500