

General purpose ovens

Basic drying and heating applications



- Ideal for basic drying or heating applications
- Maximum temperature 250°C
- Over-temperature protection
- Manually adjustable damper for increased air circulation
- Digital controller
- Stainless steel interior
- Two year parts and labour warranty
- CE marked
- Two wire shelves included as standard
- Extra shelves also available separately



Specifications and ordering information

Cat. No	15805911	15825911	15845911
Chamber size, L	65	105	176
Convection	Gravity	Gravity	Gravity
Temperature range	50 to 250°C	50 to 250°C	50 to 250°C
Uniformity at 150°C	± 4.5°C	± 5°C	± 4.5°C
Stability at 150°C	± 0.4°C	± 0.4°C	± 0.4°C
Internal dimensions (d x w x h) mm	414 x 328 x 480	414 x 438 x 580	589 x 438 x 680
External dimensions ¹ (d x w x h) mm	565 x 530 x 720	565 x 640 x 820	738 x 640 x 920
Shelves supplied/max	2/13	2/16	2/19
Shelf load, kg	25	25	25
Extra shelf Cat. No	15846392	15856392	15866392
Shelf dimensions, mm	312 x 386	422 x 386	422 x 561
Electrical/Plug type	230V, 50/60Hz, 1550W, 6.7A CEE7/7 plug for EU and BS1363/A for UK	230V, 50/60Hz, 1400W, 6.1A CEE7/7 plug for EU and BS1363/A for UK	230V, 50/60Hz, 1400W, 6.1A CEE7/7 plug for EU and BS1363/A for UK
Energy consumption at 150°C	194W	261W	320W
Unit weight, kg	42	48	67

¹Depth of handle/display not included in depth (65mm), adjustable feet not included in height (35mm) – required distance to rear wall: 80mm

Note: All figures in table are typical average values for series devices, based on factory standard following norm DIN12880.

Find out more at eu.fishersci.com/go/fisherbrand

Austria: +43 (0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20
Germany: +49 (0)2304 9325 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478
Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00
Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303
Sweden: +46 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500

 **fisher scientific**
part of Thermo Fisher Scientific